# **OMB** 452



# **OMB** 452



The OMB 452 model series are programmable, three-color panel bargraphs with auxiliary display and adjustable LCD scale. The instruments are designed as dimensional replacement of the ZEPAKOMP instruments. Available are types UNI, PWR and UQC.

Type OMB 452UNI is a multifunction instrument with the option of configuration for 8 different types of input, easily configurable in the instrument menu.

The instrument is based on an 8-bit microcontroller with multi-channel 24bit sigma-delta converter, which secures high accuracy, stability and easy operation of the instrument.

## **OMB** 452UNI

DC VOLTMETER AND AMMETER PROCESS MONITOR OHMMETER THERMOMETER FOR PT/CU/NI/TERMOCOUPLES DISPLAY UNIT FOR LINEAR POTENTIOMETERS

#### **OMB** 452PWR

AC VOLTMETER AND AMMETER AC NETWORK ANALYSER

OMB 452UQC UNIVERSAL COUNTER

## OPERATION

Option

The instrument is set and controlled by two control keys and a turn knob located on the front panel. All programmable settings of the instrument are implemented in three setting modes.

 $\ensuremath{\text{LIGHT}}$   $\ensuremath{\text{MENU}}$  is protected by optional number code and contains solely items necessary for instrument setting

**PROFI MENU** is protected by optional number code and contains complete instrument setting

 $\mbox{USER MENU}$  may contain arbitrary items from the programming menu (LIGHT/ PROFI), which determine the right (see, change). Access w/o password.

Standard equipment is the OM Link interface, which together with operation program enables modification and filing of all instrument settings as well as perform firmware updates (with OML cable). The program is also designed for visualization and filing of measured values from more instruments.

All settings are stored in the EEPROM memory (they hold even after the instrument is switched off).

## OPTION

**COMPARATORS** are assigned to monitor one, two, three or four limit values with relay output. The user may select limits regime: LIMIT/DOSING/FROM-TO. The limits have adjustable hysteresis within the full range of the display as well as selectable delay of the switch-on in the range of 0...99,9 s. Reaching the preset limits is signalled by LED and simultaneously by the switch-on of the relevant relay.

DATA OUTPUTS are for their rate and accuracy suitable for transmission of the measured data for further projection or directly into the control systems. We offer an isolated RS232 and RS485 with the ASCII/MESSBUS/MODBUS/PROFIBUS protocol.

ANALOG OUTPUTS will find their place in applications where further evaluating or processing of measured data is required in external devices. We offer universal analog output with the option of selection of the type of output - voltage/current. The value of analog output corresponds with the displayed data and its type and range are selectable in menu.

MEASURED DATA RECORD is an internal time control of data collection. It is suitable where it is necessary to register measured values. Two modes may be used. FAST is designed for fast storage (40 records/s) of all measured values up to 8 000 records. Second mode is RTC, where data record is governed by Real Time with data storage in a selected time segment and cycle. Up to 266 000 values may be stored in the instrument memory. Data transmis sion into PC via serial interface RS232/485 and OM Link.

## STANDARD FUNCTIONS

## PROGRAMMABLE PROJECTION

Selection: of input type and measuring range Measuring range: adjustable as fixed or with automatic change (DHM) Scale: LCD, freely programmable

Measuring modes (PWR): voltage (V\_{\rm RMS}), current (A\_{\rm RMS}), real power (W), frequency (Hz) and with calculation of Q, S, cos fi

Setting (UQC): measuring mode 2x counter (UP/DW, IRC)/2x frequency/timer/clock with adjustable calibration coefficient, time base and projection

Setting: manual, in menu optional projection on the display may be set for both limit values of the input signal

Projection: 50 LED + 6-digit auxiliary display

## COMPENSATION

Of conduct (RTD, OHM): automatic (3- and 4-wire) or manual in menu (2-wire) of conduct in probe (RTD): internal connection (conduct resistance in measuring head) of CJC (T/C): manual or automatic, in menu it is possible to perform selection of the type of thermocouple and compensation of cold junctions, which is adjustable or automatic

### LINEARIZATION

Linearization (DC, PM, DU): through linear interpolation in 50 points (solely via OM Link)

## DIGITAL FILTERS

Filtration constant (UQC): transmits input signal up to 10...2 000 Hz Floating/Exp./Arithmetic average: from 2...30/100/100 measurements Rounding: setting the projection step for display

#### EXCITATION

Range: 5...24 VDC, for feeding of sensors and transmitters

#### MATHEMATIC FUNCTIONS

Min/max. value: registration of min/max. value reached during measurement Tare: designed to reset display upon non-zero input signal Peak value: the display shows only max. or min. value Mat. operations: polynome, 1/x, logarithm, exponential, power, root, sin x and at the same time between inputs - sum, difference, product, quotient

#### EXTERNAL CONTROL

Lock: control keys blocking Hold: display/instrument blocking Tare: tare activation Resetting MM: resetting min/max value



BARGRAPH - 50 LED WITH DISPLAY AND LCD SCALE

MULTIFUNCTION INPUT (DC, PM, RTD, T/C, DU)


DIGITAL FILTERS, TARE, LINEARIZATION

Comparators • Data output • Analog output • Data record

POWER SUPPLY 80...250 V AC/DC

SIZE OF DIN 160 x 80 MM

Power supply 10...30 V AC/DC



## TECHNICAL DATA

#### PROJECTION

Display: 50 three-color LED + three-color LED for indication of the limits, 6-digit display (-999...9999+2 char.), 4x digit height 14 mm, 2x digit height 10 mm, illuminated and freely programmable LCD scale Decimal point: setting - in menu Brightness: setting - in menu

## TK: 50 ppm/°C

In: bot pump C
Accuracy: ±0.1% of range + 1 digit [for projection 9999 and 5 meas/s]
±0.15% of range + 1 digit
RTD, T/C
±0.3% (0.6/0.9%) of range + 1 digit
PWR
Accuracy of cold [unction measurement:: ±1.5°C
Rate: 0.1..40 meas/s, 0.5...5 meas/s [PWR]
Overload capacity: 2x; 10x [f < 30 ms] - not for > 250 V and 5 A
Measuring modes [PWR]; voltage (V<sub>pake)</sub>, current (A<sub>pake)</sub>, real power (W),
frequency (Hz) and with calculation 0, S, cos fi
Linearization: by linear interpolation in 50 points
Time base (UQC): 0.2...5.0 s
Calibration constant (UQC): 0.00001...999999
Filtration constant (UQC): 0.00001...999999
Digital filters: Exp./Floating/Arithmetic average, Rounding
Functions: Dfset, Min/max. value, Tare, Peak value, Mat. operations
Ext. control: H0LD, LOCK, Tare, Reset
Data record: measured data record into instrument memory
RTC - 15 ppm/°C, time-date-display value, < 265k data
FAST (UNI) - display value, < 8k data
Watch-dog: reset after 0.4 s

 $\ensuremath{\mathsf{DM}}$  Link: Company communication interface for operation, setting and update of instruments

## MEASURING RANGES

OMB 452 is a multifunction instrument available in following types and ranges

### type UNI, standard (code "O")


| DC:                | ±60/±150/±300/±1 200 mV                   |  |  |  |  |  |  |  |  |  |
|--------------------|---|--|--|--|--|--|--|--|--|--|
| PM:                | 05/20 mA/420 mA; ±2/±5/±10/±40 V          |  |  |  |  |  |  |  |  |  |
| OHM:               | 0100 Ω/01/10/100 kΩ/Auto                  |  |  |  |  |  |  |  |  |  |
| RTD:               | Pt 50/100/500/1 000                       |  |  |  |  |  |  |  |  |  |
| Cu:                | Cu 50/100                                 |  |  |  |  |  |  |  |  |  |
| Ni:                | Ni 1 000/10 000                           |  |  |  |  |  |  |  |  |  |
| T/C:               | J/K/T/E/B/S/R/N/L                         |  |  |  |  |  |  |  |  |  |
| DU:                | Linear potentiometer (min. 500 Ω)         |  |  |  |  |  |  |  |  |  |
| type UNI, Option A |   |  |  |  |  |  |  |  |  |  |
| DC:                | ±0,1/±0,25/±0,5/±2/±5 A; ±100/±250/±500 V |  |  |  |  |  |  |  |  |  |
| type PWR           |   |  |  |  |  |  |  |  |  |  |
| input U:           | 010/120/250/450 V                         |  |  |  |  |  |  |  |  |  |

input U: 0...10/120/250/450 V input I: 0...60/150/300 mV; 0...1/2,5/5 A

#### type UQC

Measuring mode [UQC]: input frequency 0,002 Hz..1 MHz (500 kHz for QUADR and UP/DW) 2x UP or DW counter, UP or DW counter + frequency, UP/DW counter, UP/DW counter for IRC + frequency, timer/ clock/phase

#### CONNECTION



\*GND (input + Option A) is galvanically connected with inputs EXT. and the OM Link connector \*In case of Option B we recommend to connect termianIs GND (main board/additional board) by external connection

Calibration: at 25°C and 40% r.h.

#### COMPARATOR

Type: digital, setting in menu, contact switch < 30 ms Limits: -99999...999999 Hysteresis: 0...999999 Delay: 0...99,9 s Dutput: 1...4x relays Form A (250 VAC/50 VDC, 3 A),

# 2x/4x open collector, 1...4x bistabil relays

Protocol: ASCII, MESSBUS, MODBUS - RTU, PROFIBUS Data format: 8 bit + no parity + 1 stop bit (ASCII) 7 bit + even parity + 1 stop bit (Messbus) Rate: 600...230 400 Baud 9 600 Baud...12 Mbaud (PROFIBUS) RS 232: isolated RS 485: isolated, addressing (max. 31 instruments)

#### ANALOG OUTPUT

Type: isolated, programmable with 16-bit D/A converter, type and range are selectable in programming mode Non-linearity: 0,1% of range

TK: 15 ppm/°C Rate: response to change of value < 1 ms Ranges: 0...2/5/10 V, ±10 V, 0...5 mA, 0/4...20 mA (comp. < 600 0/12 V or 1 000 0/24 V)

#### EXCITATION

Adjustable: 5...24 VDC/max. 1,2 W

#### POWER SUPPLY

### MECHANIC PROPERTIES

Material: Noryl GFN2 SE1, incombustible UL 94 V-I Dimensions: 160 x 80 x 80 mm Panel cutout: 160 x 70mm

#### OPERATING CONDITIONS

Connection: connector terminal board, section < 1,5/2,5 mm<sup>2</sup> Stabilization period: within 15 minutes after switch-on Working temperature: -20°...80°C Cover: IP64 (front panel only) Et. safety: EN 61010-1, A2 Dielectric strength: 4 kVAC after 1 min between supply and input 4 kVAC after 1 min between supply and data/analog output 2,5 kVAC after 1 min between input and data/analog output 2,5 kVAC after 1 min between input and data/analog output

 $\label{eq:linear} \begin{array}{l} \mbox{Insulation resistance: for pollution degree II, measuring cat. III. \\ \mbox{Power supply > 670 V (ZI), 300 V (DI) } \\ \mbox{input, output, Exc. > 300 V (ZI), 150 V (DI) } \\ \mbox{EMC: EN Fi326-1} \end{array}$ 

#### Seismic capacity: IEC 980: 1993, par. 6 SW validation: class B, C in compliance with IEC 62138, 61226

PI - Primary insulation, DI - Double insulation

# CONNECTING INDIVIDUAL INPUTS

DC PM 0...5/0...20 mA/4...20 mA

INPUT "U" ±60/±150/±300/±1200 mV ±2/±5/±10/40 V

#### ORDER CODE SPECIFICATION

|     | UNI  | PWR - U    | PWR - I        | UQC                               |
|-----|--|------------|----------------|-----------------------------------|
| w/o | standard                                     |            |                |                                   |
| A   | ±0,1/±0,25/±0,5//±2/±5 A<br>±100/±250/±500 V |            |                | standard<br>contact, TTL, NPN/PNP |
| в   | Expansion about three<br>inputs (PM)         |            |                | SSI input                         |
| С   |  |            |                | line input                        |
| к   |  |            | 060/150/300 mV |                                   |
| Р   |  |            | 01/2,5/5 A     |                                   |
| S   |  | 010/120 V  |                |                                   |
| U   |  | 0250/450 V |                |                                   |
| z   | on request                                   | on request | on request     |                                   |

## ORDER CODE

| OMB 452                     |                        |                    |        |          | -[ |        |    |   |   |   | 1 |   |   | - |
|-----------------------------|------------------------|--------------------|--------|----------|----|--------|----|---|---|---|---|---|---|---|
| Туре                        |                        | U                  | Ν      | I        |    | •      | •  | • | • | • | • | • | • |   |
| Order code shall not includ | le blank spaces!       | P<br>U             | W<br>Q | R*<br>C* |    | •      | •• | • | • | • | • | • | • |   |
| Power supply                |                        | 1030<br><b>250</b> |        |          |    | 0<br>1 |    |   |   |   |   |   |   |   |
| Option, see table "Orde     | er code specification' |                    |        |          |    |        | ?  |   |   |   |   |   |   |   |
| Comparators                 |                        |                    |        | none     |    |        |    | 0 |   |   |   |   |   |   |
|                             |                        | 1x relay           | (For   | m C)     |    |        |    | 1 |   |   |   |   |   |   |
|                             | 2>                     | relays             | (For   | m C)     |    |        |    | 2 |   |   |   |   |   |   |
|                             | 3>                     | relays             | (For   | m C)     |    |        |    | з |   |   |   |   |   |   |
|                             | 4x relays (Form C)     |                    |        |          |    |        |    | 4 |   |   |   |   |   |   |
|                             | 2x apen collectors     |                    |        |          |    |        |    | 5 |   |   |   |   |   |   |
|                             | 4x                     | : open (           | collec | ctors    |    |        |    | 6 |   |   |   |   |   |   |
| 2×                          | open collectors + 2>   | relays             | (For   | m C)     |    |        |    | 7 |   |   |   |   |   |   |
| Analog output               | t no                   |                    |        |          |    |        |    |   | 0 |   |   |   |   |   |
|                             | yes (Compensatio       | on < 60            | Ο Ω/   | 12 V]    |    |        |    |   | 1 |   |   |   |   |   |
|                             | yes (Compensation      | < 1 00             | D Ω/2  | 24 V]    |    |        |    |   | 2 |   |   |   |   |   |
| Data output                 |                        |                    | 1      | none     |    |        |    |   |   | 0 |   |   |   |   |
|                             |                        |                    | RS     | 232      |    |        |    |   |   | 1 |   |   |   |   |
|                             |                        |                    | RS     | 485      |    |        |    |   |   | 2 |   |   |   |   |
|                             |                        |                    | мор    | BUS      |    |        |    |   |   | 3 |   |   |   |   |
|                             |                        | F                  | ROF    | IBUS     |    |        |    |   |   | 4 |   |   |   |   |
| Excitation                  |                        |                    |        | yes      |    |        |    |   |   |   | 1 |   |   |   |
| Data record                 |                        |                    |        | no       |    |        |    |   |   |   |   | 0 |   |   |
|                             |                        |                    |        | RTC      |    |        |    |   |   |   |   | 1 |   |   |
|                             | FA                     | ST (onl            | y for  | UNI)     |    |        |    |   |   |   |   | 2 |   |   |
| Colour of digital disp      | olay                   |                    |        | red      |    |        |    |   |   |   |   |   | 1 |   |
|                             |                        |                    | g      | reen     |    |        |    |   |   |   |   |   | 2 |   |
| Other                       | customer versi         | on, do             | not 1  | fill in  |    |        |    |   |   |   |   |   |   |   |
|                             | SW validation - IEC 6  | 2138, II           | EC 6   | 1226     |    |        |    |   |   |   |   |   |   |   |

For complete technical parameters of OMB 452UQC see the universal counter OM 602UQC

\* Launch for sale has not been set